

The MRS-1100A Modular Rework System is an integrated convection rework system for the removal and reflow of BGA/CSP and SMT components.

The MRS-1100A is comprised of a hand held convection tool, preheater, adjustable tool holder, and free-standing board holder to create a manually assisted rework system. A series of nozzles, targeting a variety of applications, and optional light magnifier round out the product offering for this system.

With standard features such as programmability, a digital display, program storage of up to 50 profiles, this system is not only versatile, but also easy and efficient to work with. A choice of board holders and accessories are available that make the system capable of handling multiple sizes of PCBs.

The MRS-1100A allows you the choice of using either the embedded profiling capability that can be configured to operate at a fixed temperature, or a four zone programming option. The unit also allows the temperature to be controlled either at the heat output (internal) or at the board (external). The "external" control function uses a thermocouple which can be placed on the board or a component.





Configure the System to your Needs.

The 4 components below can be purchased as a complete system (MRS-1100A) or as separate items.

HCT-1000 Programmable Hand Held Convection Tool

The HCT-1000 System is a fully programmable hand held convection rework tool that can both remove and place SMT components. It features digital controls, in-ternal or external thermocouple feedback control, program storage of up to 50 profiles and integrated vacuum pick-up for component placement and removal. Additionally, with multiple modes of operation including manual, 4 zone heating, and as part of the MRS-1100A System, the HCT-1000 stands out as a versatile convection tool.

The hand-piece features vacuum and reflow buttons allowing the process to be operated manually or automatically through a profile when used as part of the Modular Rework System (MRS). Additionally, the vacuum has automatic lift off of components, at the end of the removal profile, taking guesswork out of the operators' hands and improving process control.

As part of the MRS System, the HCT-1000 is connected via a cable to the PCT-1000, and may be used with ATH-1100A Adjustable Tool Holder. In this mode the HCT-1000 provides timing control for both units and the ATH-1100A al-lows repeatable place and remove operations.

ATH-1100A Adjustable Tool Holder

The ATH-1100A Adjustable Tool Holder is designed to work with the HCT-1000 oars part of the MRS-1100A System. The tool holder uses the Advanced Head Assembly which features 4" of Z axis adjustment, $\frac{1}{2}$ " fine adjustment of the X & Y axis as well as 30° θ adjustment. It also features locking hand-piece retainer, Z axis stop and mounting configurations for stand-alone operation or integrated as part of the MRS-1100A. The ATH-1100A is sturdy and easy to attach to the PCT-1000 Programmable Preheater when incorporated into the MRS System.

PCT-1000 Programmable Preheater

The PCT-1000 is a programmable preheater that provides users the ability to increase heat capacity with highly controlled thermal output. The PCT-1000 can be used in a variety of processes including soldering, desoldering, SMD rework operations and, with its added heat capacity, will provide faster production rates while lowering overall process temperatures.

The preheater can be used in two modes; manual for constant heater temperature, and profile for greater control to maintain PCB board temperature with external thermocouple feedback.

With four programmable heating zones and one cooling zone, users select time and temperature targets, creating a preheat thermal profile. The PCT-1000 also has an advanced heater control function where the temperature is controlled either at the heater output (internal) or at the board (external thermocouple).

The PCT-1000 is equipped with an advanced convection heater creating a vortex effect that efficiently directs and concentrates heat.

BH-2000 Board Holder

The BH-2000 is a free-standing board holder that provides a solid and stable base for a variety of PCB's. The unit features easily adjustable rails to accommodate boards 8" (203mm) x 12" (305mm).









MRS-1100A Features

- Digital display for repeatable temperature settings and profile control
- Automatic control of the preheater for simple operation
- Easy profile creation for operator repeatability
- Integrated vacuum pickup for easy component removal
- Hand held or tool holder mounted for operator comfort
- Manual mode for quick setup
- External thermocouple for process setup and verification
- Digital controlled airflow for repeatable results
- X, Y, Z and Theta controls for component alignment
- Adjustable PCB holder for easy change outs
- Automatic vacuum lift off at the end of the cycle
- Password lockout of programmed profiles

MRS-1100A Applications

The MRS-1100A is perfect for removal and reflow of SMT Components. Specific examples of applications include:

- Simple removal and replacement of delicate SMTcomponents.
- Quick, easy and cost effective removal of BGA & CSP that will later be placed with your dedicated Array Package Rework System, this increases the productivity of your rework area and reduces your technicians workload.
- Automatically lifts the component at the end of the cycle preventing operators from prematurely lifting components and damaging expensive PCBs.

ACCESSORIES

Light Magnifier Add-on

The LM-1000A Light Magnifier is an integrated light and magnifier. It features a 4x magnification lens and an integrated LED lighting system for shadow free illumination. Supplied with base plate. The LM-1000A includes: LM-1000 Light Magnifier and LM-BP base plate.

Adjustable Tool Holder Option

The ATH-1100A can be attached to the PCT-1000 or used as a standalone unit thanks to its base plate.

ATH-BASE Optional Base plate for ATH-1100A.

Other Board Holder Options

BH-1000

Post-Rail Board Holder (incl. 4 posts, 2 rails with sliding clips, 4 supportpins and flat-head support)

BH-PK1000

Board Holder Pin Kit (incl. 2 discs, 2 long pins, 2 short pins)

BH-PK1000

HCT-NC

Nozzles for HCT-1000

A series of 14 Nozzles are available for use with the MRS-1100A / HCT-1000. The nozzles fit applications reworking components of all sizes from (including, but not limited to) BGAs, QFPs, LGAs, PLCC and SOIC. A custom nozzle program is also available.

HCT-NC

Carrier for HN Series Nozzles

Other Accessories for HCT-1000

HCT-FS2

Footswitch, Dual, HCT-1000

HCT-HTRASSY

Heater Assembly

AC-TCK-40-36

Thermocouple 40 AWG, pack of 2



LM-1000A













HN Series Nozzles





Systems and Nozzles Selection

Part Number MRS-1100A	Description Modular Rework System Advanced.
	Incl.: HCT-1000, PCT-1000, ATH-1100A and BH-2000
HCT-1000	Programmable Hand-Held Convection Tool Incl.:
HCT-PS1000	HCT-1000 Power Supply
HCT-HV1	Hand-piece with integral vacuum, cord and connector
HCTA-VC50-5	Vacuum Cup, 3/16" (5.00mm), pack of 5
HCTA-VC64-5	Vacuum Cup, 1/4" (6.4mm), pack of 5
HCTA-VC80-5	Vacuum Cup, 5/16" (8mm), pack of 5
HCTA-VC11-5	Vacuum Cup, 7/16" (11mm), pack of 5
HCTA-TH1	Hand-piece Tool Holder
HNA-1	Nozzle Adapter
HCTA-NW1	Nozzle Wrench
AC-TCK-36-36	Thermocouple 36 AWG, pack of 2
HCTA-CC	Communications Cable 4ft
HN-J0005	5mm ∅ nozzle
ATH-1100A	Adjustable Tool Holder, Advanced Head (no base)
PCT-1000	Programmable Preheater Incl.:
AC-TCK-36-36	Thermocouple 36 AWG, pack of 2
PCT-FS1	PCT-1000 Foot Switch
BH-2000	Free Standing Board Holder



* For the nozzle internal dimension, 2mm have been added to each side to allow for component access.

Nozzles Component Dimension* HN-B0707 7mm X 7mm, CSP, LGA44 HN-B1010 10mm X 10mm, CSP, LGA178, LCC28 HN-B1414 14mm X 14mm HN-B1408 14mm X 8mm, CSP, SOIC24M HN-B1515 15mm X 15mm, BGA HN-B1818 18mm X 18mm, PLCC44,CSP, TQFP100, BGA HN-B2525 25mm x 25mm, BGA , PLCC68 HN-B1809 18.2mm X 8.5mm,SOJ28, SOIC28M, TSOP32 HN-B2519 24.5mm X 18.5mm, QFP100, QFP80 HN-B2727 27mm X 27mm, BGA HN-B3535 35mm X 35mm, BGA HN-B3535 35mm X 35mm, BGA HN-B4040 40mm X 40mm, BGA HN-B4040 5 5mm ∅, DISCRETE

Authorized Distributor Mectronics Marketing Services


313, 2nd Floor, Patparganj Industrial Area,

New Delhi - 110092 (India)

Tel : +91 (011)-43041581 / 42208256

E-Mail: mectronics@mectronics.in

Web: www.mectronics.in



TECHNICAL SPECIFICATIONS

		PCT-1000 F	ICT-1000	
Size		13" x 8" x 3" (330 x 20		
Weight		7.5 lbs (3.4kg)	12 lbs. (5.4kg)	
Rated Power		1200 W	600 W	
Input Voltage	ut Voltage		Hz 100-240 VAC, 50/60 Hz	
Storage Temperatu	re	0°C to 50°C (32°F to	122°F) 0°C to 50°C (32°F to 122°F)	
Air Flow		19 cfm	5-25 l/minute	
Vacuum Pump			15" Hg (381mm Hg)	
Noise Level			<55 dB	
Source Temperature Range		25°C to 400°C (77°F	to 752°F) Up to 450°C (840°F)	
Operational Modes		Setup, Run, Manual,	Setup, Run, Manual, Active Setup	
Display			LCD 20 x 4 display segments	
Number of Programs		50 memory locations	50 memory locations	
Number of Zones 5 (4 Heat Zones, 1 Cool I		ool Down Zone)		
LM-1000A		BH-2000		
Magnification	4x	maximum board size	8" x 12" (203mm x 305mm)	
Lighting	8 LEDs, white	maximum thickness	25" (6mm)	

Power

Lens Size

24 V DC

90 mm diameter